

Selleys Supa Glue Strong & Adjustable

Description

Selleys Supa Glue Strong & Adjustable is great for all types of household repairs. The thick gel consistency means repairs with no mess. It allows extra time to align or reposition surfaces, for perfect results. It requires no mixing, gives a strong bond in seconds and dries clear. And of course, you know that if it's Selleys it works!

Product Information

Packaging	Size	Colour
Tube	3g	Clear

Uses

Selleys Supa Glue Strong & Adjustable is suitable for bonding variety of porous and non-porous surfaces, including metals, wood, china, rubber, leather (test first as some leather may become hardened or discoloured) and some plastics.

Features

- Non-drip gel consistency is ideal for vertical jobs
- More time to arrange and reposition
- No immediate finger bonding
- Bonds a variety of surfaces
- Water resistant
- No clamping necessary
- No mixing required
- Self piercing, clog free cap
- Forms a rigid bond
- Can be used for gap filling due to gel consistency

Technical Details

Property	Typical Result
Technology	Cyanoacrylate
Colour	Clear
Density	1.12
Tensile Strength ASTM D-2095 Steel-to-steel	12-22 N/mm ²
Tensile Shear Strength ASTM D-1002 Steel-to-steel	12-22 N/mm ²
Full Cure Time	24 hours
Service Temperature	-15 to 82 °C
Indicative data only, not intended for preparation of specifications	

Surface Preparation

Ensure surfaces to be bonded are clean, dry, free of dust and close fitting.

Directions for Use

- Remove nozzle and pierce tube seal with reverse end of cap and replace nozzle.
- Remove cap and apply a small amount of glue to one surface. Bring surfaces together and apply slight pressure.
- Allow 45 minutes for sufficient bond strength for practical use. Maximum bond strength reached after 12 hours.
- Wipe tip of tube, replace cap and store upright in dry cool place.

Clean Up

Remove excess from the nozzle with tissue dipped in acetone.

In case of eye contact, flush with plenty water for over 15 minutes, call a physician immediately. Use in well-ventilated place. Avoid contact clothing, it can cause very strong heat.

Access adhesive can be treated by acetone.

Storage

Store in a cool, dry place away from direct sunlight and ensure tube is well sealed.

Limitations

- Adhesive will stick to skin, but it is delayed 10 to 30 seconds, depending in skin type and amount of adhesive.
- Supa Glue Strong & Adjustable can create a white residue on the surface of a material if the area is not well ventilated. Clean the affected area with acetone, to remove residue.
- Not recommend for polyethylene, polypropylene plastics or glass.
- Not suitable for use on items that contain hot liquids e.g. mugs.
- For best results, ensure surfaces to be bonded are clean, free of dust, dry and close fitting.
- Since Supa Glue Strong & Adjustable cures with moisture, set times may be extended on very dry surfaces or under dry conditions.
- Supa Glue Strong & Adjustable cure more slowly when large amounts are used. For faster cure use sparingly.
- Do not squeeze tube before removing cap. Handle tube by plastic nozzle neck when opening and closing cap. This prevents pressurizing tube which may force material into cap, preventing a tight seal after use.

Selleys Supa Glue Strong & Adjustable

Warnings, First Aid and Shipping Information

This information can be located on the product SDS found through our website – www.selleys.com